

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1301050034](#)  
**Status:** **Active**  
**Overview:** [Specialty Lighting](#)  
**Description:** Watertite® Wet Location 30W 12V Spotlight with In-line Transformer, Switch Screw Release Guard, 14/2 SOOW, Overall Length 7.62m (50.0')

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

**Agency Certification**

CSA LR85374

**General**

Product Family Portable Lighting  
Series [130105](#)  
NEMA Configuration NEMA 5-15  
NEMA Rating NEMA 4X  
Outlet None  
Overview [Specialty Lighting](#)  
Product Literature Order No 987650-8053  
Product Name Watertite®  
Type Hand Lamps, Specialty Light  
UPC 78678861560  
Woodhead Yes

**Physical**

Cord Length - Primary 3.04m (10.0')  
Cord Length - Secondary 15.24m (50.0')  
Depth N/A  
Duty Wet Location  
Guard Included No  
Guard Type N/A  
Height 127.00mm (5.000")  
Length 228.60mm (9.000")  
Material - Guard #10 Gauge Vinyl Coated Steel  
Mounting Style Hand Held  
Packaging Type Carton  
Socket Construction N/A

**Electrical**

Bulb Type Quartz Halogen  
Cord Type - Primary 16/3 SOOW  
Cord Type - Secondary 14/2 SOOW  
Lamp Type PAR36  
Lamp Wattage - Maximum 30W  
Lumens 300  
On/Off Switch Yes  
Voltage (Fixture) - Maximum 120VAC 60 HZ  
Voltage (Secondary) - Maximum 12V AC

**Material Info**

Old Part Number 1610S



Series image - Reference only

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed  
ELV Not Reviewed

**Search Parts in this Series**

[130105](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION