

# 2-964338-2 Product Details

[Share](#) [Print](#) [Email](#)



✔ Active

## MAG-MATE Terminals

MAG MATE CONTACT MK II

**2-964338-2** ✔

TE Internal Number: 2-964338-2

**Product Highlights** [View All](#)

- Contact
- Terminal Line = Standard MAG-MATE
- Terminal Configuration = Leaf, Mark II
- Copper-Nickel-Silicon Material
- 300 Box Series

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

**Please Note:**  
Use the Product Drawing for all design activity

Product Type Features	
Product Type	Contact
Terminal Line	Standard MAG-MATE
Terminal Configuration	Leaf, Mark II
Dimensions	
Terminal Height (mm [in])	7.90 [0.311]
Body Features	
Material	Copper-Nickel-Silicon
Magnet Wire Range (mm [AWG])	0.18 - 0.265 [31 - 33]
Plating Material	Tin

Industry Standards	
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
Packaging Features	
Packaging Method	Reel/Carton
Packaging Quantity	15,000
Other	
Series	300 Box
Brand	AMP
Proprietary Name	MAG-MATE

**Related Products**

Not quite the product you're looking for?

[Find Similar Products](#)

---

[View Part in Product Feature Selector](#)

---

[Check for Tooling](#)

**Corporate Information**

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

**Quick Links**

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

**Customer Support**

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

**Keep Me Informed**