


REVISIONS					
P	LTR	DESCRIPTION	DATE	DMN	APVD
A		RELEASED PER ECO-17-006798	16MAY2017	NN	JS



CABLE BUNDLE MANAGEMENT SYSTEM						
REF	PART No.	NDM ID	MAX DD	MIN REC CABLE DD	MAX REC CABLE DD	M NDM (g/m)
CBMS-10-P-25M	EL8658-000	10	32	5	25	2.900
CBMS-20-P-25M	EL8659-000	20	42	10	38	3.100
CBMS-40-P-25M	EL8660-000	40	58	20	52	3.700

CBMS - 10 - X - 25m

PRODUCT DESCRIPTION _____

SIZE (mm) _____

MATERIAL _____

P = PBT V0 NATO GREEN _____

REEL SIZE (m) _____

THIS DRAWING IS A CONTROLLED DOCUMENT.

DMN
N. NAGAR

10MAY2017

CHK
—

—

APVD
J. SEABOURNE

16MAY2017

NAME

TE Connectivity

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± —
FINISH —

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

0

CUSTOMER DRAWING

SIZE
A3

CAGE CODE
00779

DRAWING NO
CBMS-XX-P-25M

RESTRICTED TO
—

TE

CABLE BUNDLE
MANAGEMENT SYSTEM
25m SPOOL

SCALE
DNS

SHEET
1

OF
1

REV
A