Part Number : 15045104
Product Description : 2.54mm SL Interim Clip, 10 Circuits, Polarized
Series Number : 70013
Status : Active
Product Category : Connector Accessories
Engineering Part Number : 70013-1010



Documents and Resources

Drawings

015045104_sd.pdf

700130000-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-70400-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	70013
Description	2.54mm SL Interim Clip, 10 Circuits, Polarized
Component Type	Interim Clip
Product Name	SL
UPC	800753605107

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Flammability	94V-0
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	1.550/g
Number of Rows	2
Packaging Type	Bag
Polarized to Mating Part	Yes

Downloaded from Arrow.com.

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
SL Single Row Crimp Housings and CPA Retainers	70066
SL Female Terminals	70058
SL Single Row Female Insulation Displacement Connector Assemblies	70400
SL Single Row Female Receptacles	70430
SL Dual Row Crimp Housings	70450

Downloaded from Arrow.com.