

Product Line

- Single Pair Ethernet >
- ZConnect >
- Ceres >
- Accessory
- Large Size
- Macro Size
- Middle Size
- Mini Size
- Others (GBD)
- Others (MAB)
- Others (PLD)
- Standard Size**
- X-Lok >
- M Series >
- FLDS & FLDS+ >
- Power >
- RBL >
- HS-Lok >
- NM51-0000



BD-05BFMA-SL7001

Operating Temperature: -40°C ~ +105°C
 Transmission Speed: N/A
 Shielded: Plastic, Non-shielded
 Jacket Material: N/A
 Certificate: N/A

You must login first for view the price

Quantity

[Add to Cart](#) [Inquiry](#)

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type [Search](#)

Ceres, Standard Size...

Ceres, Standard Size...

Ceres, Standard Size...

Ceres, Standard Size...

ABOUT AMPHENOL LTW **SUPPORT** **PARTNERS** **DOWNLOAD CENTER** **FEEDBACK**

- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >

- 0 +

- 0 +

- 0 +

- 0 +

[Add to Cart](#) [Inquiry](#)

Specifications	Download / CAD
Nominal Current 5A	Connector Type Field Installable
Shielded Plastic, Non-shielded	No. of Contacts 05
Connector Gender Female	Backshell Straight
Mating Style Screw Thread	IP Rating IPX7
Assembly Style Solder	

[+ More Options](#)

People Also Bought

