

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- Accessory
- Middle Size
- Mini Size
- Large Size
- Standard Size
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



DC-05AFFM-QL8E01

- Operating Temperature: -20°C ~ +105°C
- Transmission Speed: N/A
- Shielded: Plastic, Non-shielded
- Jacket Material: PVC
- Certificate: UL2238, UL50e

You must login first for view the price

Quantity

- 1 +

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

X-Lok, Large Size...

AB-DC05ML-DCB...

-20°C ~ +105°C

- 0 +

X-Lok, Large Size...

AB-DC05ML-DCB...

-20°C ~ +105°C

- 0 +

X-Lok, Large Size...

AB-DC05ML-DCB...

-20°C ~ +105°C

- 0 +

X-Lok, Large Size...

AB-DC05ML-DCB...

-20°C ~ +105°C

- 0 +

X-Lok, Large Size...

AB-DC05ML-DCB...

-20°C ~ +105°C

- 0 +

X-Lok, Large Size...

AB-DC05ML-DCB...

-20°C ~ +105°C

- 0 +

Add to Cart

Inquiry

Specifications	Download / CAD
Nominal Current 20A	Connector Type Overmolded
Shielded Plastic, Non-shielded	No. of Contacts 05
Connector Gender Female	Backshell Straight
Mating Style Push Lock	IP Rating IP68
Assembly Style N/A	
<div><div></div>More Options</div>	

People Also Bought

DC-05AFFM-QL8E01

BD-04AFMM-LL6A02

M12B-05BMMM-...

AB-DC05FR-DCBR-...

BD-02BMMMA-QL8SP0

[ABOUT AMPHENOL LTW](#)

[SUPPORT](#)

[PARTNERS](#)

[DOWNLOAD CENTER](#)

[FEEDBACK](#)

Downloaded from [Arrow.com](#)