


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
00	NEW RELEASE	18.08.20	QG


Cable Length	Part Number
1.0m(+0.05m/-0m)	FO-10GGBLCX20-001
2.0m(+0.10m/-0m)	FO-10GGBLCX20-002
3.0m(+0.10m/-0m)	FO-10GGBLCX20-003
4.0m(+0.10m/-0m)	FO-10GGBLCX20-004
5.0m(+0.10m/-0m)	FO-10GGBLCX20-005
6.0m(+0.10m/-0m)	FO-10GGBLCX20-006
10.0m(+0.10m/-0m)	FO-10GGBLCX20-010
15.0m(+0.10m/-0m)	FO-10GGBLCX20-015

B

B



LC CONNECTOR SET



A

A

N0	PART NAME
1	DUST CAP
2	PLUG HOUSING(BEIGE)
3	BARREL/FERRULE
4	SPRING
5	EXTENDER CAP(BEIGE)
6	CRIMP SLEEVE
7	CLIP(BEIGE)
8	BOOT (WHITE)

Specification

1. Marking: Amphenol Cables on Demand 10 GIGABIT OPTICAL FIBER CABLE LSZH xx/xx xxxxM
2. Fiber: Multimode 50/125um OM3 Optical Fiber
3. Fiber cord: 2.0*4.2mm ,LSZH Color Aqua
4. Operating wavelength: 850nm
5. Insertion Loss: $\leq 0.3\text{dB}$



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		EAR NO.		Amphenol Cables on Demand	
		APPROVALS	DATE	20 VALLEY ST. ENDICOTT, NY 13760	
DECIMALS	ANGLES	DRAWN	Lojing	2.0*4.2mm Aqua LSZH LC-LC OM3 Patchcord	
.X	ii.X	CHECKED	Qingguo		
.XX	ii.XX	RESP ENG		SIZE DWG. NO.	
.XXX	ii.XXX				
THIRD ANGLE PROJECTION		MFG ENG		FO-10GGBLCX20-XXX	
CAD FILE:				REV. 00	