






OGA DIAGONAL: 11.62 [295.18]
VA DIAGONAL: 10.84 [275.46]
PA DIAGONAL: 10.25 [260.26]



(SER)
EXII-7720SC
98-0003-2217-6
SERIAL CONTROLLER
SOLDER SIDE

(USB R)
EXII-7760UC
98-0003-2814-0
USB CONTROLLER
SOLDER SIDE



TOP LEVEL NUMBER	US NUMBER	CHINA NUMBER	TYPE	DM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-8021-203	98-0003-2503-9	59-0000-0096-4	FFC	4.27" [108.46]	AG500	23655
17-8021-205	98-0003-2504-7	59-0000-0097-2	FFC	8.00" [203.20]	AG500	23655
17-8021-206	98-0003-2505-4	N/A	NOV	SEE DWG	AG500	23655
17-8021-221	98-0003-2507-0	59-0000-0099-8	SFR	4.27" [108.46]	AG500	23655
17-8021-227	98-0003-2510-4	59-0000-0101-2	SFR	8.00" [203.20]	AG500	23655
17-8021-218	98-0003-2916-3	59-0000-0098-0	USB R	4.27" [108.46]	AG500	23655
17-8021-226	98-0003-2509-6	59-0000-0100-4	USB R	8.00" [203.20]	AG500	23655

PINOUT
1 LR
2 LL
3 SHED
4 UL
5 UR

NOTES:

1. WEIGHT OF GLASS IN GRAMS: 32.1 ± 10%
2. NICOMATIC HOUSING P/N: 0105
3. NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
4. HOUSING ORIENTED WITH LATCH DOWN

MARKETING DRAWING
SCT32NN 10.84"

REV	DATE	CHG	BY	APP
G	9/11	SB		
F	8/11	SB		
05	10/09	AH		

3M TOUCH SYSTEMS
3M TOUCH, WA
USA

THIS DOCUMENT IS THE PROPERTY OF 3M TOUCH SYSTEMS, INC. AND IS NOT TO BE REPRODUCED OR USED FOR ANY OTHER PURPOSES WITHOUT THE WRITTEN PERMISSION OF 3M TOUCH SYSTEMS, INC.

UNITS	INCHES [MM]
TOLERANCES UNLESS OTHERWISE SPECIFIED	
X .XX ±.03 [.76]	
.XXX ±.015 [.38]	
ANGLES ±1°	
THIRD ANGLE PROJECTION	
DO NOT SCALE DRAWING	
SCALE 1 = 1	

SIZE	DOCUMENT NO.	SHEET	REV
C	28209-MKT	1 OF 1	G