

D-Sub_CCH_S2_PP_PL_PLA_FC



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 67 015 0210 160 |
| Specification | D-Sub_CCH_S2_PP_PL_PLA_FC |
| HARTING eCatalogue | https://harting.com/09670150210160 |

Identification

| | |
|-----------------------------|------------------|
| Category | Hoods / Housings |
| Series | D-Sub |
| Type of hood/housing | Shell housing |
| Description of hood/housing | Cover lockable |

Version

| | |
|---------------|--|
| Size | D-Sub 2 |
| Shielding | Shielded |
| Version | Top/side entry |
| Cable entry | 3x |
| Cable fixing | Cable clamp |
| Locking type | PushPull |
| 2 parts | Yes |
| Separable | Yes |
| Details | An external InduCom cable clamp or a crimp flange - ferrule combination can be used to gain more space in the housing. |
| Pack contents | 2 blind plates internal cable clamp with screws |

Technical characteristics

| | |
|--|---------------------------|
| Tightening torque | 0.35 Nm Cable clamp screw |
| Ambient temperature | -20 ... +90 °C |
| Mating cycles | ≥500 |
| Degree of protection acc. to IEC 60529 | IP30 |

Page 1 / 2 | Creation date 2026-04-10 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
 Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com



Pushing Performance
Since 1945

Technical characteristics

| | |
|----------------------|--|
| Cable diameter | 3.3 ... 14 mm Please follow the assembly instructions! |
| Vibration resistance | Category 1B acc. to IEC 61373 |
| Shock resistance | Category 1B acc. to IEC 61373 |

Material properties

| | |
|---|------------------------|
| Material (hood/housing) | Thermoplastic |
| Surface (hood/housing) | Metallised |
| Colour (hood/housing) | RAL 7032 (pebble grey) |
| Material flammability class acc. to UL 94 | HB |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Not contained |

Commercial data

| | |
|--------------------------------|---------------------|
| Packaging size | 10 |
| Net weight | 31.167 g |
| Country of origin | China |
| European customs tariff number | 85389099 |
| GTIN | 5713140469990 |
| eCl@ss | 27440213 D-Sub hood |
| UNSPSC 24.0 | 39121416 |