

## Han 3A-gw-M20 +gekl.Dicht.



Image is for illustration purposes only. Please refer to product description.

Part number	19 20 003 0626
Specification	Han 3A-gw-M20 +gekl.Dicht.
HARTING eCatalogue	<a href="https://harting.com/19200030626">https://harting.com/19200030626</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han A <sup>®</sup>
Type of hood/housing	Hood
Description of hood/housing	for Han-Brid <sup>®</sup> With glued seal

### Version

Size	3 A
Version	Side entry
Number of cable entries	1
Cable entry	1x M20
Locking type	Single locking lever
Field of application	Standard Hoods/housings for industrial applications
Pack contents	Please order seal screw separately.

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw



Pushing Performance  
Since 1945

## Technical characteristics

	4
Type rating acc. to UL 50 / UL 50E	4X
	12

## Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	10
Net weight	13.04 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140124462
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466