

TPS Straight Clamp Plug RG-58 RG-141 Times LMR-195 50 Ohm

033-7015-7

Find In Stock & Buy Now

TPS Straight Clamp Plug RG-58 RG-141 Times LMR-195 50 Ohm

+ Add To Parts List

☰ Add To Compare

Product Compliance

- RoHS (EU). Compliant with Exemption 6C - [View Certificate](#)
- California residents see [Prop 65 Warning](#)
- Additional compliance information is available in our [Compliance Center](#).

Description

RF Connector TPS Straight Clamp Plug RG-58 RG-141 Times LMR-195 50 Ohm

Product Life Cycle

Part Status	Active
-------------	--------

Product Specifications

Body Finish	Silver
Body Material	Brass
Cable Type (Terminates to)	RG-58, RG-141, Times LMR-195, Times LMR-200-LLPL, Belden 7806A, Belden 8219, Belden 8240, Belden 8259, Belden 8262, Belden 9201, Belden 9203, Belden 9310, Belden 9311
Contact Finish	Gold
Contact Material	Brass
Contact Termination	Solder
Coupling Mechanism	Bayonet
Export Control Classification Number	EAR99
Gender	Plug
IP Rating	Not Rated
Impedance (Ohms)	50
Insulator Material	PTFE
Isolated	No
Low PIM	No
Mil Qualified	No
Non Magnetic	No
Orientation	Straight
Panel Mounting Feature	Not Applicable
Ports	1 (Single Port)
Size Category	Standard
Temp (Max Degrees Celsius)	165
Temp (Min Degrees Celsius)	-65
Termination Style	Cable - Clamp

You May Also Be Interested In



TPS Straight Clamp Plug RG-303 50 Ohm

033-7298-10

Amphenol® RF

TPS Straight Clamp Plug 0.085-inch Conformable 0.086-inch Conformable RG-405 75 Ohm

033-1670-1

Need A Custom RF Cable Assembly?

Build Your Cable Now

Subscribe And Stay Connected With Amphenol RF

Enter Email Address

Submit

By submitting your email, you are agreeing to receive occasional updates from Amphenol RF. This site is protected by reCAPTCHA and the Google [Privacy Policy](#) and [Terms of Service](#) apply.

Company

About Us

Locations

Careers

Newsroom

Capabilities

Quality

Quick Links

Distributor Inventory

Competitor Cross

Reference

Compliance Center

Document Library

Quickbuild RF

Anti-Slavery/Human Trafficking

Support

Contact Us

Local Representative

Locator

Authorized Distributors

Account

Login / Sign Up

My Parts List

Extranet Login

Follow Us

