Part Number : 1212050005
Product Description : mPm DIN Valve Connector, Form C-Micro 9.4mm, External Thread, 3 Pole Plus Ground Terminal, 250V AC/DC, Black, Nitrile Gasket
Series Number : 121205
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : C29300N0T



Documents and Resources

Drawings

1212050005_sd.pdf

Specifications

PK-121205-C29-001.pdf

PS-121201-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:1844b936-2483-4d05-8313-8e067e3d77ae
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Connectors
Series	121205
Description	mPm DIN Valve Connector, Form C-Micro 9.4mm, External Thread, 3 Pole Plus Ground Terminal, 250V AC/DC, Black, Nitrile Gasket
IP Rating	IP65, IP67
Product Name	mPm
Type	Field Attachable Connector
UPC	884982350458

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Form	C - Micro 9.4mm
Gender	N/A

Downloaded from Arrow.com.

Keyway	None
Material - Connector Body	Polyamide
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	13.033/g
Orientation	90° Angle
Pitch - Mating Interface	9.40mm
Poles	3
Temperature Range - Operating	-40° to +90°C
Wire Size (AWG)	N/A

Downloaded from Arrow.com.