


CROSS SECTION THRU FLAT

Part Number	Count	Pairs	A Span	B Span
125-3017-068	68	34	1.701 ± 0.012	1.675 ± 0.010
125-3017-080	80	40	2.001 ± 0.012	1.975 ± 0.010

Alternative Twist Lengths Available, Consult Factory for
Ordering Information.

All Dimensions in Inches, Unless Otherwise Noted

PHYSICAL

Conductors: 30 AWG 7/38 Tinned Copper
Insulation: .006" TPO
Color Code: 1st Pair Red/White followed by
Orange/White and Repeat
Laminate: Polyester
Temperature Rating: 80°C

ELECTRICAL

Impedance: 90 ± 6 ohms¹ 122 ± 5 ohms²
Capacitance: 17 pF/ft @ 1 MHz¹ 11 pF/ft @ 1 MHz²
Propagation Delay: 1.45 ns/ft
Voltage Rating: 150 V
Current Rating: 0.75 A
DC Resistance: 106 ohm per 1,000 ft @ 20°C

¹ Above values measured Single-Ended, with one conductor
of each pair commoned to one Buss(SCSI Mode)

² Above values measured Differentially.

Approvals: UL AWM Style 20744
CSA AWM

Print Legend: **Amphenol SPECTRA-STRIP**

UL® AWM 80C LL31941 CSA AWM I A80C 150V FT-1
30 AWG Stranded Ultra 320 SCSI™ Compliant <Date Code>
Spectra-Green Lead Free/PBB Free

DRAWN	PROD ENG	QA	MKT	P/ECN#	DRAWING NO. 125-3017-068 & -080	AMPHENOL SPECTRA-STRIP 720 SHERMAN AVE TEL (203) 281-3200 HAMDEN CT 06514 FAX (203) 281-5872	Rev E
FITS 11/2/99	8/3/04			772	TITLE: .025" Twist 'N' Flat		SHEET 1 of 1
					Full Lamination, 30 AWG 7/38		