



PC board drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S90C4PL00LF	D09S90C6PL00LF
15	39.14	33.32	25.18	24.54	19.18	D15S90C4PL00LF	D15S90C6PL00LF
25	53.03	47.04	39.12	38.25	33.12	D25S90C4PL00LF	D25S90C6PL00LF
37	69.32	63.50	55.68	54.71	49.68	D37S90C4PL00LF	D37S90C6PL00LF
						200 matings	500 matings

rev	ecn no	dr	date
A	LS08-0039	MPE	2008/02/01
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	PESSON	2008/02/01	ANGULAR	LINEAR	0.X	± 0.1	size A3	Scale 2		
Eng	PESSON	2008/02/01			0.XX	± 0.1				
Chr	LEGARE	2008/02/01			0.XX ± 2°	± 0.1				
Appr	LEGARE	2008/02/01	Product family			D-SUB		Spec ref -		
			FEMALE CONNECTOR				dwg no C-8646-0903			Rev. A
			straight press-fit							
			catalog no -				CUSTOMER sheet 1 of 1			

REV F - 2006-04-17