

Part Number : [1301100050](#)

Product Description : Pro-Yellow 400W Metal Halide
High Bay Light with Lamp Molded 18/3 SJTW 1.83m
(6.0') Pulse Start

Series Number : 130110

Status : Obsolete

Product Category : Lamps and Lights

Engineering Number : 8575-MH-PS



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Lamps and Lights
Series	130110
Description	Pro-Yellow 400W Metal Halide High Bay Light with Lamp Molded 18/3 SJTW 1.83m (6.0') Pulse Start
NEMA Configuration	NEMA 5-15
NEMA Rating	Rain Tight
Product Name	Pro-Yellow
Type	Wide Area Lamps
UPC	78172505741

Agency

UL	E174253
----	---------

Electrical

Lamp Wattage - Maximum	400W
Lumens	26000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Metal Halide - Pulse Start
Cord Length - Primary	0.91m (3.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	N/A
Duty	General
Guard Included	Yes
Guard Type	Steel
Height	463.55mm (18.250")
Lamp Type	BT37/ED-37 Type O
Length	N/A

Material - Guard	#10 Gauge Zinc-plated Steel
Mounting Style	Hook
Net Weight	6477.293/g
Outlet	None
Packaging Type	Carton

This document was generated on Sep 24, 2025

Obsolete