

Specification Sheet

Part Number: 133-02836



One-piece design allows installers to mount and bundle wire or cables single-handedly.

Wing design helps stabilize the tie in high vibration applications.

1-Piece Cable Tie/Fir Tree Mount w/Wings, 6.0" Long, 0.25 - 0.28" Hole Dia, PA66HIRHS, Gray, 3000/ctn

Article Number	133-02836
Type	T50ROSFT6.5
Color	Gray (GY)
Quantity Per	carton
Product Description	One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. Wing design helps stabilize the tie in high vibration applications.
Short Description	1-Piece Cable Tie/Fir Tree Mount w/Wings, 6.0" Long, 0.25 - 0.28" Hole Dia, PA66HIRHS, Gray, 3000/ctn
Global Part Name	T50ROSFT6.5-PA66HIRHS-GY

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	222
Length L (Imperial)	6.0
Length L (Metric)	151.7
Fixation Method	Fir tree for round holes
Identification Plate Position	none
Releasable Closure	No
Width W (Imperial)	0.19
Width W (Metric)	4.8
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2
Height H (Imperial)	0.59

Height H (Metric)	15.1
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.25
Panel Thickness Min (Metric)	0.8
Panel Thickness Max (Metric)	6.3
Mounting Hole Diameter D (Imperial)	0.25 - 0.28
Mounting Hole Diameter D (Metric)	6.3 - 7.0 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.28
Mounting Hole Diameter D Max (Metric)	7.0
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)