

Aptiv Connection Systems Catalog

Customer Service

Samples Request

Find by Feature

Browse by Category

Browse by Application

Comparison List (0)

Share

Search

Enter part number or keyword

Search Results (1)

Search Options

1 Result(s): [All] - 10762803

☐ Compare

54001400 - APEX 2.8 Female Unsealed Tin Plating Terminal Assembly, Cable Range 1.50 - 2.50 mm2

☐ Compare

APEX 2.8 Female Unsealed Tin Plating Terminal Assembly, Cable Range 1.50 - 2.50 mm2

Part # 54001400



[Question about this product?](#)

Attributes

Part # :	54001400
Description :	APEX 2.8 Female Unsealed Tin Plating Terminal Assembly, Cable Range 1.50 - 2.50 mm2
Product Type :	Terminal
Status :	✓ Active
Blade size [mm] :	2.8
Series :	2.8
Gender :	Female
Sealable :	Unsealed
Material :	CuTeSn/CuBe
Weight [g] :	1
Plating :	Tin
Minimum Cable Diameter [mm] :	2.10
Maximum Cable Diameter [mm] :	2.80
Minimum Cable Core Cross Section [mm2] :	1.31
Maximum Cable Core Cross Section [mm2] :	2.08
Remarks :	Former FCI Product, Delphi PN:10762803, High current carrying capacity, Low contact mating force, Without Grease, Suitable for secondary lock

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.