Pushing Performance
Since 1945

UNI-DICHT-HALB-Verschraubung Pg16



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5058
Specification	UNI-DICHT-HALB-Verschraubung Pg16
HARTING eCatalogue	https://harting.com/09000005058

Identification

Category	Accessories
Series of hoods/housings	Han-Compact®
Type of accessory	Cable gland
Description of the accessory	for surface mounted housings

Technical characteristics

Tightening torque	≤6 Nm (depending on the cable and the seal insert used)
Wrench size	27
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP65
Size	Pg 16
Clamping range	11.5 ... 15.5 mm

Material properties

Material (cable glands)	Thermoplastic
Colour (cable gland)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	2-(2'-Hydroxy-3'-tert-butyl-5'-methylphenyl)-5-chlorobenzotriazole (UV-326)

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Not contained

Commercial data

Packaging size	10
Net weight	6.5 g
Country of origin	Germany
European customs tariff number	39174000
GTIN	5713140001435
eCl@ss	27140807 Additional components cable gland
ETIM	EC003608
UNSPSC 24.0	39121431

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.