

Part Number : [936010914](#)

Product Description : Heavy-Duty Standard (STD) Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Side Entry, Size 6B «44x27», Extended M25 Thread, Grey

Series Number : 93601

Status : Active

Product Category : Heavy-Duty Connectors


Engineering Part Number : 7806.6552.0



Documents and Resources

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[UKCA - Declaration of Conformity](#)

[CE - Declaration of Conformity](#)

Part Details

General

| | |
|----------------|---|
| Status | Active |
| Category | Heavy Duty Connectors |
| Series | 93601 |
| Description | Heavy-Duty Standard (STD) Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Side Entry, Size 6B «44x27», Extended M25 Thread, Grey |
| Component Type | Single Lever Hood |
| IP Rating | IP66 |
| Product Name | Heavy-Duty Connectors |
| Standard | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Type | STD |
| UPC | 887191858715 |

Agency

| | |
|-----|---------|
| CSA | 256883 |
| UL | E249674 |

Electrical

| | |
|-------------------|------|
| Voltage - Maximum | 500V |
|-------------------|------|

Physical

| | |
|---------------------|------------------|
| Component Size | 6B «44x27» |
| Entry Location | Side |
| Hood Coating | Polyester Powder |
| Hood Color | GREY RAL 7037 |
| Lock to Mating Part | Yes |

| | |
|-----------------|-------------------|
| Material - Hood | Die-cast Aluminum |
| Material - Peg | Stainless Steel |
| Net Weight | 92.200/g |
| Number of Pegs | 2 |
| Packaging Type | Bag |
| Thread Size | M25 |
| Thread Type | (M) Metric |

Mates With / Use With

Use with Part(s)

| Description | Part Number |
|-------------|--|
| Use With | Size 6B «44x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts |

This document was generated on Apr 26, 2026