

Relay base - PR3-BSC1/3X21 - 2833615

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Relay base PR3..., for octal relay REL-OR with 3 PDT, screw connections, connection facility for input/interference suppression modules, for mounting on NS 35/7.5



Your advantages

- ✓ Relay base family that can be fitted with 2 PDT or 3 PDT relays



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 933838
GTIN	4017918933838
Weight per Piece (excluding packing)	66.000 g
Custom tariff number	85366990
Country of origin	China

Technical data

Dimensions

Width	38 mm
Height	75 mm
Depth with retaining bracket	84 mm (EL3-M52)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Connection data, input side

Relay base - PR3-BSC1/3X21 - 2833615

Technical data

Connection data, input side

Connection name	Input side
Connection method	Screw connection
Stripping length	10 mm
Screw thread	M3
Conductor cross section solid	0.2 mm ² ... 2.5 mm ²
	0.2 mm ² ... 2.5 mm ² (2 conductors with the same cross-section)
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
	0.2 mm ² ... 2.5 mm ² (2 conductors with the same cross-section)
Conductor cross section AWG	26 ... 14
	26 ... 14 (2 conductors with the same cross-section)

Connection data, output side

Connection name	Output side
Connection method	Screw connection
Stripping length	10 mm
Screw thread	M3
Conductor cross section solid	0.2 mm ² ... 2.5 mm ²
	0.2 mm ² ... 2.5 mm ² (2 conductors with the same cross-section)
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
	0.2 mm ² ... 2.5 mm ² (2 conductors with the same cross-section)
Conductor cross section AWG	26 ... 14
	26 ... 14 (2 conductors with the same cross-section)

General

Nominal voltage U _N	400 V AC/DC
Nominal current I _N	10 A
Color	green
Mounting position	any

Standards and Regulations

Connection in acc. with standard	CSA
----------------------------------	-----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Relay base - PR3-BSC1/3X21 - 2833615

Classifications

eCl@ss

eCl@ss 4.0	27371100
eCl@ss 4.1	27371100
eCl@ss 5.0	27371600
eCl@ss 5.1	27371600
eCl@ss 6.0	27371600
eCl@ss 7.0	27371603
eCl@ss 8.0	27371603
eCl@ss 9.0	27371603

ETIM

ETIM 2.0	EC001456
ETIM 3.0	EC001456
ETIM 4.0	EC001456
ETIM 5.0	EC001456
ETIM 6.0	EC001456
ETIM 7.0	EC001456

UNSPSC

UNSPSC 6.01	30211917
UNSPSC 7.0901	39121516
UNSPSC 11	39121516
UNSPSC 12.01	39121516
UNSPSC 13.2	39122326
UNSPSC 18.0	39122335
UNSPSC 19.0	39122335
UNSPSC 20.0	39122335
UNSPSC 21.0	39122335

Approvals

Approvals

Approvals

CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Relay base - PR3-BSC1/3X21 - 2833615

Approvals

Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	255476
UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 113228
cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 113228
EAC			RU C- DE.A*30.B.01082
cULus Recognized			