
This document was generated on 10/17/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0510894005

Status: Active

Description: 2.00mm Pitch Mi II System Wire-to-Board Crimp Housing, Dual Row, 40 Circuits, Gray



Series image - Reference only

Documents:

3D Model
Drawing (PDF)
Product Specification 510890000-PS-000 (PDF)
Product Specification PS-51089-001 (PDF)
Product Specification PS-51089-005-001 (PDF)
Application Specification AS-52484-001-001 (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	51089
Application	Signal, Wire-to-Board
Product Name	Mi II
UPC	800755527575

Physical

Circuits (maximum)	40
Color - Resin	Gray
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Polyester
Net Weight	1502.800/mg
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	AS-52484-001-001
Product Specification	510890000-PS-000, PS-51089-001, PS-51089-005-001
Sales Drawing	SD-51089-**05

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free Status
Not Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
51089 Series

Mates With
53313 , 53314

Use With
50212 Crimp Terminals

This document was generated on 10/17/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Downloaded from Arrow.com.