Specifications



Photo is representative





Eaton HCMA1305-R47-R

Eaton HCMA1305 inductor, 0.47 uH, 38 A Irms, 65 A ISAT, 0.92 mΩ resistance, SMT mounting, Iron Powder, 2-pins, 400 qty.

General specifications	
PRODUCT NAME	Eaton HCMA1305 inductor
CATALOG NUMBER	HCMA1305-R47-R
UPC	051712496056
PRODUCT LENGTH/DEPTH	13.8 mm
PRODUCT HEIGHT	5 mm
PRODUCT WIDTH	12.5 mm
PRODUCT WEIGHT	4.618 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	38 A
ISAT	65 A
PACKAGE QUANTITY	400
MATERIAL	Iron powder
AUTOMOTIVE GRADE	Yes
FREQUENCY RATING	Up to 5 MHz
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-55 to 125 °C
RESISTANCE	0.92 mΩ
SIZE	13.8x12.5x5.0 mm
TERMINALS	2 Pads
SERIES	HCMA1305

Resources

SPECIFICATIONS AND DATASHEETS	Eaton HCMA1305 automotive high current power inductors data sheet Eaton Specification Sheet - HCMA1305-R47-R

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2026 Eaton. All Rights Reserved.

Downloaded from Arrow.com.