




**Part Number :** [2261961024](#)

**Product Description :** Mini-Fit Versa Color-to-Mini-Fit Versa Color Off-the-Shelf (OTS) Cable Assembly, 4.20mm Pitch, Dual Row, 600.00mm Length, 2 Circuits, Red

**Series Number :** 226196

**Status :** Active

**Product Category :** Power and Signal Cable Assemblies



---

## Documents and Resources

### Drawings

[2261961024 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Power and Signal Cable Assemblies
Series	226196
Description	Mini-Fit Versa Color-to-Mini-Fit Versa Color Off-the-Shelf (OTS) Cable Assembly, 4.20mm Pitch, Dual Row, 600.00mm Length, 2 Circuits, Red
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Mini-Fit Versa Color-to-Mini-Fit Versa Color
Product Name	Mini-Fit Versa Color
Type	Discrete Wire Assembly
UPC	198282202295

### Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

### Physical

Cable Length	600.00mm
--------------	----------

Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Red
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	22.762/g
Number of Rows	2
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	4.20mm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1007
Wire Size (AWG)	16

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Mini-Fit Jr. Dual Row Plug Housings	<u><a href="#">46993</a></u>
Mini-Fit Vertical Dual Row Headers	<u><a href="#">172447</a></u>

---

This document was generated on Apr 29, 2026