


LAYOUT FOR P.C.B.  
CONNECTOR SIDE VIEW



spec ref	---	dr	Sky Chen	2013-12-24	projection	MM	size	A3	scale
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	Sky Chen	2013-12-24	product family	dwg no	ecn no	rel level	Released
ASME Y14.5M	chr	Terris Liu	2013-12-24						
	appr	PM Zheng	2013-12-24						
	surface	✓	linear	0.X 0.XX 0.XXX	±0.2 ±0.10 ±	FCI	METRAL VT HDR - 24WAY SOLDER TAILS/WIDE BODY		rev
			angular	0°	±2°	www.fci.com	cat. no.	Product - Customer Drw	sheet 1 of 1
							C-8626-11114		E

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE PRODUCT SPECIFICATION GS-12-446

NOTE-1: 2 PEGS AT EACH END ONLY

NOTE-2: CAVITY FOR CODING KEY MOUNTING AND CABLE CONNECTOR LATCH.

NOTE-3: IF SUFFIX "P" IS ADDED IN P/N PACKAGING IS IN TRAYS  
BUT CONNECTOR MARKING IS WITHOUT "P"

EXAMPLE:HMIW4IDTR400H6P, MARKED HMIW4IDTR400H6

NOTE-4: P.C.B HOLES DEFINITION - SEE GS-12-446

NOTE-5: A SYMBOL WILL BE NEXT TO ANY DIMENSION,VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

SPECIFIC DATAS:

Visual inspection : 100%

- Marking failures
- Housing material failures
- Spoilt housing
- Stained housing
- Broken contacts ( twisted or loosen )