








APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/23/19	
A		UPDATE DRAWING.	4/22/21	WX/TL



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Shell: Copper Alloy

Plating:

Gold flash over Nickel underplate overall

Electrical:

Current rating: 1,5PIN 1.8A Max.

2,3,4PIN 1.0A Max.

Contact resistance: 30 milliohms max.

Insulation resistance: 100 Megohms min.

Dielectric withstand voltage: 100 VAC for 1 minute

Temperature Rating:

Operating temperature: -30°C to +80°C

Environmental:

Lead free, RoHS compliant.



PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ±.10	ØX ±.10
.XX ±.020	ØXX ±.015
.XXX ±.015	ØXXX ±.010

DRAWN	AY	4/23/19
CHECKED	TW	4/23/19
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH**ADAM
TECH**909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE		MICRO USB, TYPE B, SINGLE PORT FEMALE, TRUE SMT TYPE, TAPE & REEL	
SIZE	PART NO.	REV.	
X	MCR-B-S-RA-TSMT-NP-CS4-G-T/R	A	
REF:	S00097C	SCALE:	NTS
SHEET		1 OF 1	