


# Product data sheet

Specifications



## Condenser, 46kW, 115F(46C),208-230V/3, 60Hz

ACCD75229

### Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

### Main

Main Input Voltage	200 V 3 phases 208 V 3 phases 220 V 3 phases 240 V 3 phases
--------------------	--

### General

Air discharge option	Horizontal Upflow
Air flow	7868.31 l/s
Inrush current	10 A

### Physical

Height	82.4 cm
Width	97.7 cm
Depth	315.1 cm
Net weight	230.88 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable
Length	3.15 m

### Input

Minimum circuit ampacity	12 A
Network frequency	60 Hz
Maximum overcurrent protection	15 A

### Conformance

Product certifications	ETL
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental

Ambient air temperature for operation	-20...50 °C
Operating altitude	0...10000 ft
Audible noise at 1 meter from surface of unit	65 dBA

Packing Units

Package 1 Weight	272.16 kg
Package 1 Height	88.9 cm
Package 1 width	109.2 cm
Package 1 Length	330.2 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------