








REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	LEN-7A0012	2007/10/01	Zeus	Added Note
D	LEN-040046	2010/03/30	Vicky	REF. TO ECR/N.NOTE.
E	LEN1370285	2013/07/19	Rensong	chang demension 25.2 to 25.3



Pin Assignment
Front View



Recommended Panel Cut-Out



Note:

- * $\varnothing$ Important Dimension.
- * Waterproof Rate: IP68.
IP68: 1M Depth Of Water In 24hours.
- * Housing: Nylon+GF, Black.
- * Female Pin: Copper Alloy, Gold Plated.
- * Shield: Zinc Alloy, Nickel Plated.
- * Nut: Zinc Alloy, Nickel Plated.
- * O-Ring1: EPDM, Black.
- * O-Ring2: Viton, Green.
- * For Panel Thickness Max 4.5mm.
- * Nut Torque: 4-6 Kgf.cm

UNIT:mm		TITLE M12 Conn Panel Screw 5Pin F Conn F Pin			
TOLERANCE		SCALE 2:1	SIZE A4	SHEET 1 OF 1	REV. E
.X ±0.25		WC-REV. B.1	$\varnothing$: Inspection item		
.XX ±0.1					
.XXX ±0.05					
ANGLES ±1°					

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO 12-05PFFS-SF8001	DRAWN BY Lin_rensong	DATE 2013-07-19
DWG NO 12-05PFFS-SF8001	CHECKED BY Tony	DATE 2013-07-19
CUSTOMER ALTW	APPROVED BY Maslow	DATE 2013-07-19