Part Number : 1301470084
Product Description : Watertite Extreme Extra Hard Outdoor Plug with Locking Blade, 3 Pole/4 Wire, NEMA L17-30, 3ø 600V, Cord Grip Body Size F4, Black
Series Number : 130147
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 28W77BLK



Documents and Resources

Drawings

1301470084_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130147
Description	Watertite Extreme Extra Hard Outdoor Plug with Locking Blade, 3 Pole/4 Wire, NEMA L17-30, 3ø 600V, Cord Grip Body Size F4, Black
IP Rating	IP69K
NEMA Configuration	NEMA L17-30
Product Name	Watertite Extreme
Specialty	N/A
Type	Plug
UPC	78678871387

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	30.0A
GFCI	No
Voltage - Maximum	3Ø 600V

Physical

Cord Grip Body Size	F4 1"
Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Male

Downloaded from Arrow.com.

Length	N/A
Lighted Connector	No
Locking Blade	Yes
Poles	3-pole/4-wire
Receptacle Type	N/A

Downloaded from Arrow.com.