



Part Number : 1301430126

Product Description : Watertite Extreme Cordset 12 Gauge SJOW, 2 Pole/3 Wire, Cordset Length 15.24m, NEMA 5-20 125V, Inline GFCI

Series Number : 130143

Status : Active

Product Category : Wiring Devices

Engineering Number : 14W33B123IN

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices
Series	130143

Description	Watertite Extreme Cordset 12 Gauge SJOW, 2 Pole/3 Wire, Cordset Length 15.24m, NEMA 5-20 125V, Inline GFCI
IP Rating	IP67
NEMA Configuration	NEMA 5-20
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	N/A
Type	Cordset
UPC	78678871017

Agency

CSA	LR6837
UL	E38085

Electrical

Current - Maximum per Contact	20.0A
GFCI	Yes-In-line
Voltage - Maximum	125V

Physical

Cord Grip Body Size	F2 1/2"
Cord Type	12/3 SJOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	15.24m (50.0')
Lighted Connector	No
Locking Blade	No
Net Weight	666.000/kg
Poles	2-pole/3-wire
Receptacle Type	Single

This document was generated on Jul 03, 2024