


C-171507



PARTS NUMBER	STUD	H DIMENSION	INS. DIA
171507-1	1/4	6.73	2.03 ~ 3.18
-2	5/16	8.33	2.03 ~ 3.18
OBSOLETE -3	1/4	6.73	2.66 ~ 3.56
OBSOLETE 171507-4	5/16	8.33	2.66 ~ 3.56

G	OBSOLETE	Y.O	N.Y	14APR17
F	Change Applicable Body	Y.O	N.Y	23JAN17
E	REVISED (P-DWG)	X.Y	N.Y	4/1/18
D	REVISED (P-DWG)	S.O	N.Y	1/1/17
C	ADDED MARK	H.S	N.Y	7/1/15
B	REVISED (REL.3)	N.S	N.Y	7/1/15
A	REVISED (P-DWG)	H.S	N.Y	12/1/14
C	REVISED (P-DWG)	H.S	N.Y	10/1/14
4	REVISION RECORD:	DR	CHK	DATE

H	REVISED PER ECR-17-017886	E.T	N.Y	08DEC17
---	---------------------------	-----	-----	---------

1975 BY AMP CORP. L.L.C. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.	参考図面 (CUSTOMER COPY REFERENCE ONLY)
MATERIAL: COPPER (電気銅)	TE Connectivity
TIN PLATING: 鍍めつき	
WIRE GAUGE: 0.26 ~ 1.04 (AWG 22-18)	
WIRE TYPE: 2-1-1 (2-1-1)	
TOLERANCE: 4-1	J A C-171507 H

丸型 端 WIRE TERMINAL ASSEMBLY