



Pushing Performance
Since 1945

M5 A-cod 4-pol st/- m/- PUR 2.0M



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 030 0413 020
Specification	M5 A-cod 4-pol st/- m/- PUR 2.0M
HARTING eCatalogue	https://harting.com/21340300413020

Identification

Category	System cabling
Series	Circular connectors M5
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M5 A-coding Male Straight
Type of cable	Copper cable (round)

Version

Cable length	2 m
Number of cores	4
Core structure	4x 0.25 mm ²
Coding	A-coding

Technical characteristics

Limiting temperature	-25 ... +80 °C
----------------------	----------------

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Pushing Performance
Since 1945

Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	567c8b78-5fa0-43aa-a4c0-beb9d99b7769
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Specifications and approvals

Approvals	CE
-----------	----

Commercial data

Packaging size	1
Net weight	58.5 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140283428
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC001855
UNSPSC 24.0	26121604