



Part Number : 02065108
Product Description : 1.57mm Diameter,
Standard .062" Pin and Socket Crimp
Terminal, Female, with Selective Gold (Au)
Plated Brass Contact, 24-18 AWG, Reel
Series Number : 1561
Status : Active
Product Category : Crimp Terminals
Engineering Number : 1561-(P228)
Packaging Alternative : 02065109 (Bag)




Documents & Resources

Drawings
[002065108_sd.pdf](#)
[15610000-PK-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	1561
Description	1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with Selective Gold (Au) Plated Brass Contact, 24-18 AWG, Reel
Application	Power, Wire-to-Wire
Product Name	Standard .062"
UPC	800753615755

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.080/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.05mm
Wire Size (AWG)	18, 20, 22, 24
Wire Size mm ²	N/A

Application Tooling

Global

Description	Part Number
-------------	-------------

Insertion Tool for Standard .062" Diameter Male and Female Terminals	<u>11020001</u>
Extraction Tool for Standard .062" and Standard .062"+ Pin and Socket Terminals	<u>11030002</u>
Terminator Die	<u>11402004</u>
ServiceGrade Hand Crimp Tool for Field Repair Only, 24-14 AWG	<u>638111000</u>
Hand Crimp Tool for Standard 1.57mm Pin and Socket Crimp Terminals, 24-18 AWG	<u>638191300</u>
Mini-Mac Applicator for Standard .062" Pin and Socket Terminals, for 24-18 AWG Wire with Insulation Diameter 1.52-3.05mm	<u>638914000</u>

This document was generated on Apr 26, 2025