Part Number : 1200700237
Product Description : M12 Signal, A-Coded, Bulkhead Receptacle, 5 Poles, Female to Male
Series Number : 120070
Status : Active
Product Category : Circular Industrial Connectors
Engineering Part Number : 8R5L30



Documents and Resources

Drawings

1200700237_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Triphenyl-phosphate per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120070
Description	M12 Signal, A-Coded, Bulkhead Receptacle, 5 Poles, Female to Male
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	M12 Signal,Micro-Change (M12)
Type	Bulkhead Feed-Through
UPC	78678845499

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC/DC

Physical

Coupling Type	Internal Thread
Gender	Female-Male
Keyway	A-Coded
Length	N/A
Material - Component	Nickel-plated Brass
Mounting Thread Size	M12 x 1.0
Net Weight	45.250/g
Orientation	Straight

Downloaded from Arrow.com.

Panel Mount	Front
Poles	5
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	N/A
Wire Size (AWG)	N/A

Downloaded from Arrow.com.