



Part Number : [1301040041](#)
Product Description : Haztex Incandescent
Hazardous and Wet Location Hand Lamp, 100W
Series Number : 130104
Status : Active
Product Category : Lamps and Lights
Engineering Number : 61430



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130104
Description	Haztex Incandescent Hazardous and Wet Location Hand Lamp, 100W
Comments	Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)
NEMA Configuration	N/A
NEMA Rating	NEMA 4X
Product Name	Haztex
Type	Hand Lamps, Specialty Light
UPC	78678861430

Agency

CSA	LR39801
UL	E30252

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Incandescent
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	127.00mm (5.000")
Duty	Hazardous, Wet Location
Guard Included	Yes

Guard Type	Cast Aluminum
Height	419.10mm (16.500")
Lamp Type	A21
Length	N/A
Material - Globe	Tempered Soda-Lime Glass
Material - Guard	Cast Aluminum
Mounting Style	Hand Held
Net Weight	2.720/kg
Outlet	None
Packaging Type	Carton

This document was generated on Sep 10, 2025