



Pushing Performance
Since 1945

Han D F Crimpkontakt 2,5 mm² GT/SMC



Part number	09 15 000 6406
Specification	Han D F Crimpkontakt 2,5 mm² GT/SMC

Identification

Category	Contacts
Series	Han D®
Type of contact	Crimp contact

Version

Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	2.5 mm²
Conductor cross-section	AWG 14
Rated current	≤10 A
Contact resistance	≤3 mΩ
Stripping length	6 mm

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Han®-GoldTec
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	100
Net weight	0.61 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140022386
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors