



UG-556B/U N-Type Straight Clamp Jack RG-58 RG-141 Times LMR-195 Bulkhead 50 Ohm

000-35275

Find In Stock & Buy Now

UG-556B/U N-Type Straight Clamp Jack RG-58 RG-141 Times LMR-195 Bulkhead 50 Ohm

+ Add To Parts List Add To Compare

Product Compliance

- RoHS (EU). Compliant with Exemption 6C - [View Certificate](#)
- California residents see [Prop 65 Warning](#)
- Additional compliance information is available in our [Compliance Center](#).

Description

UG-556B/U N-Type Straight Clamp Jack RG-58 RG-141 Times LMR-195 Bulkhead 50 Ohm

Product Life Cycle

Part Status	Active
-------------	--------

Product Specifications

Alias	35275
Body Finish	Nickel
Body Material	Brass
Cable Type (Terminates to)	RG-58, RG-141, Times LMR-195, Times LMR-200-LLPL, Belden 7806A, Belden 8219, Belden 8240, Belden 8259, Belden 8262, Belden 9201, Belden 9203, Belden 9310, Belden 9311
Contact Finish	Silver
Contact Material	Beryllium Copper
Contact Termination	Solder
Coupling Mechanism	Threaded
Export Control Classification Number	EAR99
Frequency (Max GHz)	18
Gender	Jack
IP Rating	Not Rated
Impedance (Ohms)	50
Insulator Material	PTFE
Isolated	No
Low PIM	No
Mil Qualified	No
Non Magnetic	No
Orientation	Straight
Panel Mounting Feature	Bulkhead - Rear Mount
Ports	1 (Single Port)
Size Category	Standard
Temp (Max Degrees Celsius)	165
Temp (Min Degrees Celsius)	-65
Termination Style	Cable - Clamp
Thread Direction	Standard

You May Also Be Interested In



Amphenol®RF

Amphenol®RF



SMP RA PL to SMP RA PL 0.047 Hand Formable 50 Ohm 5 in
095-725-121-005

SMA Panel Mount Jack 4-Hole Flange Flat Tab 50 Ohm
901-9215-3CCSF

SMA Panel Mount Jack 2-Hole Flange Solder RG-405 0.086-inch Conformable Times Tflex 402 50 Ohm
901-9246-10

N-Type Str Pl to N-Type Str Pl AA-60091 50 Ohm 60 in
095-909-164-060

SMP RA PL to SMP RA PL 0.047 Hand Formable 50 Ohm 50 mm
095-725-121M005

Need A Custom RF Cable Assembly?

Build Your Cable Now

Subscribe And Stay Connected With Amphenol RF

Enter Email Address

Submit

By submitting your email, you are agreeing to receive occasional updates from Amphenol RF. This site is protected by reCAPTCHA and the Google [Privacy Policy](#) and [Terms of Service](#) apply.

Company

About Us
Locations
Careers
Newsroom
Capabilities
Quality

Quick Links

Distributor Inventory
Competitor Cross
Reference
Compliance Center
Document Library
Quickbuild RF
Anti-Slavery/Human Trafficking

Support

Contact Us
Local Representative
Locator
Authorized Distributors

Account

Login / Sign Up
My Parts List
Extranet Login

Follow Us

