



Search within category

GO

BUY NOW

DESIGN / INSTALL



**FX1BN3NNNSNM002**

OM3 1-fiber, SC to pigtail, 900µm buffered fiber, patch cord, no jacket, (one SC connector on one end and open on the other end), Std. IL.

Specs

Documents

★ Add to Favorites

🛒 Add to BOM

Std. Pkg. Qty.	1
Fiber Type	OM3 50/125µm
Flammability Rating	Riser (OFNR)
Fiber Count	1
Connector 1 Type	SC Simplex
Connector 2 Type	Pigtail
Cable Length Range	0-9 m (0-32 ft)
Length (ft.)	7
Length (m)	2
Cable Color	Aqua
Assembly Length Range	0-9 m (0-32 ft)
RoHS Compliancy Status	Compliant
Min. Order Qty.	1.0000