0916 - 0920 Push Button Switches *0.5A 250Vac*

Self-Wiping - Slow Make & Break

In house test **0.5A 250Vac T85**

RoHS **RoHS compliant**

µ contact gap.

Technical data on pages 4 & 5.

- Self wiping contacts
- Slow make & break
- Momentary action
- Choice of switch circuits
- Choice of actuators



T0916S0 - - -
& T0916L0 - - -


T0916VA - - -

T 0916 S O - - -

TERMINAL FUNCTION ACTUATOR BODY COLOUR

TERMINAL

T



Solder

FUNCTION

0916



Black base

SP ON-OFF (momentary ON)


0917 50V only



Brown base

SP ON-ON (momentary 1 side)

0918



White base

SP ON-OFF (momentary OFF)

0919



Black base

SP ON-ON (momentary 1 side)

0920



White base

DP ON-OFF (momentary ON)

ACTUATOR


S
Small Actuator



L
Large Actuator



V
Vandal Resistant IP66
Flat top Stainless steel



BODY


O
for L and S Actuator



Panel Cut-out

Panel thickness
Both nuts - 2.5mm
No backnut - 4.0mm

A
for V Actuator (stainless steel)
Chamfer profile bezel



Panel Cut-out
Panel thickness - 8.0mm


OPTIONS

Finish
Gloss finish for L and S actuators.

Colour
Call factory for custom colours.
A full range is available for large orders.


Dimensions (mm)

Nylon S and L actuators



Neck thread - 40 TPI Whit. Actuator travel - 2.5 max

Stainless steel V actuator (IP66)



Neck thread - 26 TPI Whit. Actuator travel - 2.5 max

Downloaded from Arrow.com.