

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5055670271

Status:


Active

Overview:

Micro-Lock Plus Connector System

Description:

1.25mm Pitch, Micro-Lock Plus PCB Header, Right-Angle, Surface Mount, Tin-Bismuth Plating, Positive Lock, 2 Circuits, Black



Documents:	
Drawing (PDF)	Application Specification 5055650000-AS-000 (PDF)
3D Model	Application Specification AS-505565-001-001 (PDF)
3D Model (PDF)	Packaging Specification 5055679200-200 (PDF)
Product Specification 2145260000-PS-000 (PDF)	Datasheet (PDF)
Product Specification 5055650000-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 5055651000-PS-000 (PDF)	

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	505567
Application	Signal, Wire-to-Board
Component Type	PCB Header
Overview	Micro-Lock Plus Connector System
Product Name	Micro-Lock Plus
Taxonomy	PCB Headers and Receptacles
UPC	889056508186
Physical	
Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin-Bismuth
Material - Plating Termination	Tin-Bismuth
Material - Resin	Polyamide
Net Weight	118.190/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Plating min - Mating	1.000µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	Vacuum Pick-Up Area
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

505567 Series

Mates With

Micro-Lock Plus Receptacle Housing

505565 . Micro-Lock Plus Cable Assembly

45111

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	5055650000-AS-000, AS-505565-001-001
Packaging Specification	5055679200-200
Product Specification	2145260000-PS-000, 5055650000-000, 5055651000-PS-000
Sales Drawing	5055670000-SD-000

This document was generated on 01/03/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION