



Rev	AWO #	Description	Date	Appr
-		RELEASED	1/20/15	

APPROVED: _____
DATE: _____ TITLE: _____



PCB LAYOUT



SPECIFICATIONS:
Material: Nylon 66, rated UL 94V-0
Insulator color: White
Contacts: Brass
Plating: Tin over Copper underplate overall
Electrical:
Operating voltage: 250 VAC max
Current rating: 7 Amps max
Contact resistance: 10 mohms max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 1,500 VAC for 1 minute
Temperature Rating:
Operating temperature: -25°C to +85°C
Environmental:
Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES [MM] TOLERANCES: EXCEPT AS NOTED		INCHES		Holes		DATE		TITLE	
.X	± .10	ØX	± .10	ØX	± .10				
.XX	± .020	ØXX	± .015	ØXX	± .015				
.XXX	± .015	ØXXX	± .010	ØXXX	± .010				
APPROVALS		DATE		TITLE		PART NO.		REV.	
DRAWN	AY	1/20/15		1/20/15		LHC-03-TS-SMT-V0-B		-	
CHECKED	LL	1/20/15		1/20/15		LHC-03-TS-SMT-V0-B		-	
APPROVED									

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

.156 [3.96] POWER HEADER, SMT
STRAIGHT, WITH REAR LOCK

SIZE X
PART NO. LHC-03-TS-SMT-V0-B
SCALE: NTS
SHEET 1 OF 1