



Part Number : [351513219](#)

Product Description : VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Yellow, Glow-Wire Capable

Series Number : 35151

Status : Active

Product Category : Connector Housings

Documents and Resources

Drawings

[351513219 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[351500000AS ENG-000.pdf](#)

[351500000AS KOR-000.pdf](#)


[PK-35151-001-001.pdf](#)

[PS-35150-001-001.pdf](#)

[PS-35150-003-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	35151
Description	VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Yellow, Glow-Wire Capable
Application	Power, Wire-to-Wire
Product Name	VersaBlade
UPC	822350608589

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	2
Color - Resin	Yellow
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	Yes

Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	PET/PC
Net Weight	1.593/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.20mm
Pitch - Termination Interface	6.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +110°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housing, 9 Circuits, Full Flange Panel Mount, Natural, Glow-Wire Capable	2026500909
VersaBlade Hybrid Receptacles Housings and TPAs	35150
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housings	35524

Use with Part(s)

Description	Part Number
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Natural	351500290
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Red	351500292
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Yellow	351500293

VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Blue	<u>351500294</u>
VersaBlade Female Crimp Terminals	<u>35746</u>

This document was generated on May 13, 2026