



MR8G98

by Burndy
Catalog ID: MR8G98

Prop 65 Notice

Full cycle ratchet tools for critical applications, #22 - #10 AWG, YAV, T, YAD Connectors, 10.56 IN L, All Steel Alloy, Body - Cast Aluminum

- Long handles provide greater mechanical advantage
- Adjustable stop for terminals (lowers for splices)
- Color-coded die grooves
- Fully protected ratchet mechanism
- Reinforced heavy duty back
- High strength aluminum body

5 year limited warranty

Product Details

General

Die Type	Permanent Dies
Tool Type	Ratchet Crimping Tool
Trade Name	HYTOOL™
Type	Crimpers
UPC	781810701072
UPC 12 Digit	7818107010722

Dimensions

Height	1.50 in
Length	10.56 in
Weight	1.5 lb
Width	3.31 in

Conductor Related

Crimping Ranges	#22 - #10 AWG
-----------------	---------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)