

[Precautions for use](#)
[General notes](#)

SA-2000-563 made in JAPAN



Order model number

Order model number	SA-2000-563[Body color]
Order example	SA-2000-563R (An example of an order with a red color.)

[Basic information](#)
[Soldering heat resistance conditions](#)
[Conformity product / Mate product](#)
[Download](#)

Body color



Basic information

Rating	30V-3A
Insulation resistance	DC 500V, 50MΩ Min
Withstand voltage	AC500V (1minute)
How to mount	With nut
Panel thickness	2.5mm MAX
Nut torque	1.0N·m Max
Main insulator	Polycarbonate
Body color	B (Black), R (Red), BL (Blue), Y (Yellow), G (Green), W (White)
Overview	Gold-plated product of TJ-563.
Mate	SA-2000-560, TJ-560, TJ-2167, TJ-100-KB attached to TJ-100.

Related products

TJ-563



[TJ-563](#)

[Add to My List](#)