

Search For

enter search text

Part Number

Home> 5973604307F

Part Number: **5973604307F**

General Description	
Series	597
Configuration	PLCC -2
Description	SMD LED PLCC BL InGaN 7" Reel
Package Options	Tape and Reel
Lamp Type	Single Color
LED Type	InGaN
Lens Color	Non - Diffused

Absolute Maximum Ratings (Ta = 25Â° °)	
Forward Current mA	30mA
Forward Current Pulsed	100mA
Derating	from 40Â° @ .42mA/Â°C
Solder Temperature	240Â° for 20 sec
Operating Temperature	-55~+100
Storage Temperature	-55~+100

Operating Characteristics	
Color	Blue
Luminous Intensity Min	45
Luminous Intensity Typical	56
Test Current mA	20mA
Dominant Wavelength Typical	470nm
Power Dissipation Max	14mW



5973604307F

check stock



This is a
RoHS Compliant Product
To learn more click here