






GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
See PRODUCT SPECIFICATION: GS-12-447

LAYOUT FOR P.C.B



NOTES:

1. MATERIAL : BODY : LCP UL94-V0
: CONTACT : COPPER ALLOY.
2. FOR PLATING PERFORMANCE REFER DRAWING # 10159409
3. CONNECTORS WITH PCB 2.4mm ARE COMPATIBLE WITH WIDE AND NARROW BODIES.
4. PLUG FOR CODING KEY FIXING.
5. FLAT ROCK INSERTION TOOLING IN PCB, SEE DRW REF : C-8626-1003.
6. METALIZED HOLE DEFINITION , SEE GS-12-447.
7. IF SUFFIX "P" IS ADDED IN P/N PACKAGING IS IN TRAYS BUT CONNECTOR MARKING IS WITHOUT "P".
EXAMPLE : HM1FXXXXXXXXHxPLF, MARKED HM1FXXXXXXXXHxLF
8. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-47- 0004
9. A△SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE
WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

X-PLATING CODE △
REF.DWG. 10159409

PART NUMBER :HM1F43FDP000HxPLF

mat'l. code				surface	tolerance	projection	product family		
				ISO 1302	ISO 406 ISO 1101		METRAL		
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM	title		
H	LS06-0095	LGO	2006-06-30	angles	linear		METRAL FEMALE 4 ROWS 96 CTS		
J	LS06-0159	MLE	2006-10-16				RIGHT ANGLE PRESS-FIT / PRESS-IN PEG		
K	LS07-0266	MLE	2007-11-06						
L	ELX-I-38656	MINI	2020-10-09	dr	ETIEMBRE	1998-05-06	dwg no	sheet 1 of 1	size
M	ELX-I-42905	NIRMAL	2021-11-12	enr	NRMAL SAM	2021-11-12	C-8626-0066		A3
				chr	ALEX BABU	2021-11-12			
				appd	SANOJ P K	2021-11-12			
sheet	revision	M					type Product Customer Drawing		
index	sheet	1							