






ASSEMBLY - VIEW FROM FRONT



ASSEMBLY - VIEW FROM SIDE



ASSEMBLY - VIEW FROM REAR





PLATE CUTOUT



EXPLODED ISOMETRIC VIEW

DNFF150**115
Finish - Front Screen - ABS Plastic
- Back Panel - ABS Plastic
Rated - 115 VAC, 50/60 Hz, 0.24 Amps
Free Flow Air Delivery - 230 CFM
Colours
DNFF150BK115 - Black
DNFF150CG115 - Gray/Beige
DNFF150GY115 - Gray
DNFF150LG115 - Light Gray
Hardware
2 Screws - Panhead Taptite 10-32 x 1/2"
2 Screws - Flathead #10-32 x 1/2"
2 Screws - Flathead Taptite #10-32 x 1/2"
2 Nuts - #10-32 Locktooth
Accessories
PFF4000 - Standard Filter Media (Pkg of 5)
PLFF4000 - Pleated Filter Media (Pkg of 5)

