USB Extension Cable (USB-A Right-Angle M to USB-A F), 10-in. (25.4 cm)

MODEL NUMBER: **U005-10I**





Highlights

- Modifies the cable connecting to a PC to 90 degrees
- 24k gold-plated connectors and gold-plated copper contacts
- 24 gauge power wires

System Requirements

- USB port and device

Package Includes

- USB 2.0 Gold Extension cable - USB "A" Right-Angle Male to USB "A" Female - 10"

Features

- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil feature twisted 28/24 AWG data lines
- Gold-plated connectors and gold-plated copper contacts provide superior conductivity
- Molded connectors with built-in strain relief ensure that the cable lasts a long time

Specifications

OVERVIEW	
UPC Code	037332117861
Technology	USB 2.0 (High Speed)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB A (FEMALE)
Connector Style	Angled
PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	0.8
Cable Length (m)	0.24
Cable Length (in.)	10

Downloaded from Arrow.com.

Cable Length (cm)	25.40
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Downloaded from Arrow.com.