

**Part Number :** [192120003](#)

**Product Description :** InsulKrimp Wire Pin Terminal  
for 22-18 AWG Wire, Bag

**Series Number :** 19212

**Status :** Active

**Product Category :** Crimp Terminals

**Engineering Part Number :** WP-2218X



---

## Documents and Resources

### Drawings

[192120003\\_sd.pdf](#)


### Specifications

[PS-19902-013-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Crimp Terminals
Series	19212
Description	InsulKrimp Wire Pin Terminal for 22-18 AWG Wire, Bag
Application	Power, Wire-to-Component
Comments	Pin Length 8.90mm
Product Name	Wire Pin,InsulKrimp
UPC	800753053335

### Agency

CSA	LR18689
UL	E32244

### Physical

Flammability	94V-0
Gender	Male
Material - Metal	Copper
Material - Plating Mating	Tin
Net Weight	0.689/g
Packaging Type	Bag
Plating min - Mating	1.016µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.68mm max.
Wire Size (AWG)	18, 19, 20, 22
Wire Size mm <sup>2</sup>	N/A

---

## Application Tooling

### Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 22-10 AWG and 6.0-0.5mm <sup>2</sup> (Rings, Spades, Hooks, Block Spades and Flanged Spades)	<u>640010100</u>
PremiumGrade Hand Crimp Tool for Insulkrimp Terminals and Splices, 22-10 AWG (Rings, Spades, Hooks, Block Spades and Flanged Spades)	<u>640010300</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640050100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640050300</u>
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	<u>640160036</u>

---

This document was generated on May 20, 2026