

Home: >

Part Number: 87897-0707

2.54mm SR Hdr RA 2.5SnLF 7Ckt

Image not available

Status:Active

Series:87897

Category:Molex Parts

Go to **Part Detail**▼

CHECK DISTRIBUTOR INVENTORY

[Add to My Parts](#)

Series image - Reference only

Specifications & Other Documents:

Sales Drawings, 3D Models, and Brochures

Documents not available online

Drawing (PDF)

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

EU ELV:Not Relevant

EU RoHS:Compliant

EU RoHS Phthalates:Not Contained

China RoHS:

REACH SVHC:Not Contained Per - ED/01/2017 (12 January 2017)

Low-Halogen Status:Low-Halogen

Product Compliance Statement

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Part Detail

COLLAPSE ALL

▼ General

Status	Active
Category	Molex Parts
Series	87897
UPC	887191659022

▼ Physical

Net Weight	668.049/mg
------------	------------

▼ Solder Process Data

Solderability Shelf Life Statement

Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

▼ Material Info

Downloaded from Arrow.com

RESOURCES

STAY CONNECTED

Antennas
Application Tooling
Cable Assemblies
Connected Lighting
Connectors
Copper Flex
Electrical Products
Industrial Automation
Membrane Switches
Optical Solutions
PCB Assemblies

Company Information
Contact Molex
Cross-Reference
Koch Industries
Industries
Literature
Press Room / Press Releases
Product Index
Sitemap

California Supply Chains Act
Compliance
ecocare
Feedback | Help
Jobs
Legal | Trademarks
Mobile Site
Supplier Portal
Privacy Policy
Tradeshows

