



Catalog No. TC92

Description: SADDLE BASE .6X.6IN NAT NYL SCREW

UPC No 5414363059370

Home > Wire & Cable Management > Ty-Rap > Cable tie mounts

Saddle-Type Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 15.11mm (0.595 Inches), Width of 15.11mm (0.595 Inches), Height of 14.27mm (0.562 Inches), Screw Mounting Method, #6 Screw

Descriptors

Category	Cable tie mounts
Special Features	Saddle Mounting Plate for use with round bundles.

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

Classifications

Brand Name	Ty-Rap
------------	--------

Dimensions

Mount Size	#6
------------	----

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	15.11 mm
Length	0.59 inch
Width	15.11 mm
Width	0.59 inch
Height	14.27 mm
Height	0.56 inch



ETIM	EC000449 Mounting base and -element for cable ties
Type of fastening	Other
Material	Plastic
Material quality	Polyamide (PA)
Colour	Natural colour